


Effect RIC F2 (M-RECEIVER)

Minimal to severe hearing losses
E7/E6/E5/E4/E3/E2



Fitting range



Key Features	E7	E6	E5	E4	E3	E2
Processing and fine-tuning channels	15	12	10	6	6	4
Experience Level Manager	•	•	•	•	•	•
Programs	5	4	3	3	3	3
Automatic Adaptive Directionality channels	15	12	10	6	6	4
Volume Control II*	•	•	•	•	•	•
Programmable Push Button**	•	•	•	•	•	•
Ambient Noise Rejection II	•	•	•	•	•	•
Noise reduction	•	•	•	•	•	Minimal
Linked ZEN	•	•	•	•	•	•
Linear Frequency Transposition	•	•	•	•	•	•
Acoustic Situation Technology	11 (IE)	7 (IE)	4	3		
Impulse Noise Rejection II	•	•	•			
Speech Enhancer	II/Linked	Linked				
Real Ear Effect	•	•				
Wind Noise Control II	•					
High-frequency boost	•					
Connectivity						
Tcoil	•	•	•	•	•	•
2.4 GHz control (Android and iOS)	•	•	•	•	•	•
2.4 GHz streaming (iOS)	•	•	•	•	•	•
DEX assistive listening device compatibility	•	•	•	•	•	•
Accessories						
Coselgi App	•	•	•	•	•	•
Acoustic remote control App	•	•	•	•	•	•
COM-DEX App	•	•	•	•	•	•

*Via DEX and app **Programmable: Volume control II, program shift or a combination of the two

Colours


069/Summer Gold, 081/Tan Silk, 118/Tech Black, 119/Silver Grey, 121/Titanium Grey, 123/Autumn Beige

TECHNICAL DATA


		EAR SIMULATOR IEC 60118-0:1983, + A1:1994	2CC COUPLER IEC 60118-0:2015, ANSI S3.22-2014
OSPL90	1600 Hz Peak Average	118 dB SPL 124 dB SPL 118 dB SPL	108 dB SPL 114 dB SPL 110 dB SPL
Acoustic output (Input 60 dB SPL)	1600 Hz Peak Average	103 dB SPL 108 dB SPL 99 dB SPL	93 dB SPL 98 dB SPL 93 dB SPL
Full-on gain (Input 50 dB SPL)	1600 Hz Peak Average	61 dB SPL 69 dB SPL 62 dB SPL	52 dB SPL 58 dB SPL 55 dB SPL
Telecoil output (Input 31.6 mA/m)		103 dB SPL 108 dB SPL 99 dB SPL	93 dB SPL 98 dB SPL 93 dB SPL
Acoustic Frequency range		100 Hz - 10000 Hz	100 Hz - 7000 Hz
Harmonic distortion (Input 70 dB SPL)	500 Hz 800 Hz 1600 Hz	<2% <2% <2%	<2% <2% <2%
Equivalent input noise		21 dB SPL	21 dB SPL
Battery current (stand by)		1.00 mA	1.00 mA
Battery current		1.02 mA	1.04 mA
Battery life / hours (Type 312 Zn-Air, 170 mAh)*		165 h	165 h
Mobile phone immunity (IEC 60118-13:2016, ANSI C63.19:2011)		IRIL: -21/-19/-9 dB SPL	U-rating: M4/T4

*Battery life in real-life situations depends among other things on the hearing aid features used, streaming time, and the quality of the battery used.


MAXIMUM OUTPUT - EAR SIMULATOR



MAXIMUM OUTPUT - 2CC COUPLER



OUTPUT - EAR SIMULATOR



OUTPUT - 2CC COUPLER

